



NBX-2

Surface Mount Box for NA-NE

- SPECIFICATIONS -



MOUNTING:

1. Attach NBX-2 to wall surface.
2. Bring wires for NA-NE through the opening in the back .
3. Connect wires to sub station.
4. Attach the the sub station to the box, using supplied screws.

SPECIFICATIONS:

Construction: 18 AWG Steel

Dimensions (H x W x D): NA-NE alone: 8-5/8" x 6-5/16" x 2".
 With NBX-2: 8-5/8" x 6-3/8" x 2-1/2".
 Without NA-NE: 1lb. 1oz.
 With NA-NE: 2 lb. 15 oz.

Weight:

Mounting hardware: Included with NA-NE