

NEM/NEM-A SYSTEM CALL SWITCH



NBR-7AS Moisture-resistant call switch with pull cord



NBR-7AS:

Dimensions;

W: 70mm(2-3/8") H: 115mm(4-1/2") D: 46mm(1-13/16")

Recessed; 30mm(1-3/16")

FEATURES

- * Call from NBR-7AS can only be cancelled at the calling site.
- * Unlike NBR-8A call button, it is not necessary to use with NB-L.
- * Max. three NBR-7AS per number line.

OPERATION

Pull down the cord or press nurse-marked button.


NEM master is called by tone and LED.

Depress a corresponding selector button and call tone stops.

The call can only be cancelled at NBR-7AS, by releasing call switch.

WIRING

When installing three NBR-7AS in parallel



Distributed by;

