

**SYSTEM/MODEL:** TD-H/B

**MODIFICATION:** Lower the call tone volume

**DIFFICULTY LEVEL:** 3 - Moderate - Removal or replacement of internal components.

**COMPONENTS REQUIRED:** 1. Resistor: 330 - 10K ohm, 1/4 Watt

**INSTR/OPERATIONS:** Remove and replace resistor R1 on PC-1440 inside the TD-nH/B phone.  
The value can be varied to obtain the desired call tone volume level.

Using a 5K ohm resistor will reduce the volume by approximately half.

**REFERENCE DRAWING #:**

Aiphone's product warranty applies to products properly modified using these instructions.  
However, if a unit is damaged as a result of improper modification, the warranty does not apply.

# LOWER THE CALL TONE VOLUME

TD-12H/B Schematic Diagram

